

Datasheet

## RS Pro M20 Grey EPDM Cable Gland, 8 to 13mm Cable Dia Range, IP67

RS Stock No: **279-7037**



### Product Details

RS Pro cable gland in grey colour, has a thread size of M32. This cable gland has a diameter ranging from 8 to 13 mm. The cable features halogen free rubber (EPDM) membrane cable grommet providing protection up to IP67.

### Features and Benefits

- Halogen free rubber (EPDM) membrane cable grommet providing protection up to IP67
- Quick and low-cost method of feeding cables through panels
- Ideal for applications where space is restricted
- Tapered top provides a degree of retention and sealing

### Specifications:

|                               |              |
|-------------------------------|--------------|
| Cable Diameter Range          | 8 to 13 mm   |
| Colour                        | Grey         |
| IP Rating                     | IP67         |
| Material                      | EPDM         |
| Maximum Cable Diameter        | 13 mm        |
| Maximum Operating Temperature | +70°C        |
| Minimum Cable Diameter        | 8 mm         |
| Minimum Operating Temperature | -50°C        |
| Operating Temperature Range   | -50 to +70°C |
| Thread Size                   | M20          |

| EPDM Rubber, RAL 7035 Grey, IP 67 (EN 60529), Wall thickness 0,5 - 5 mm, Temperature range -40°...+110°C |                 |               |          |                   |      |       |       |      |       |          |
|--|-----------------|---------------|----------|-------------------|------|-------|-------|------|-------|----------|
| Code   | Order symbol    | EAN           | Size     | Cable diameter    | A mm | B mm  | Da mm | H mm | H1 mm | Pcs/pack |
| 3545078  | FEM 4-7         | 6418074035417 | M12      | 4-7               | 12,5 | 0,5-2 | 20    | 12,7 | 5,4   | 50       |
| 3545079  | FEM 5-9         | 6418074035424 | M16      | 5-9               | 16,5 | 1-4   | 21    | 18   | 10,5  | 50       |
| 3545278  | FEM 4-7 L       | 6418074070449 | M12      | 4-7               | 12,5 | 2-5   | 20    | 12,7 | 5,4   | 50       |
| 3545279  | FEM 5-9 L       | 6418074070456 | M16      | 5-9               | 16,5 | 2-5   | 21    | 18   | 10,5  | 50       |
| 3545080  | FEM 8-13        | 6418074035448 | M20      | 8-13              | 20,5 | 1-4   | 25,5  | 20   | 12,7  | 50       |
| 3545081  | FEM 10-14/PG 16 | 6418074035455 | M23/PG16 | 10-14             | 23   | 1-4   | 28    | 21,6 | 14,7  | 50       |
| 3545082  | FEM 11-17       | 6418074035462 | M25      | 11-17             | 25,5 | 1-4   | 30,5  | 21,6 | 14,5  | 50       |
| 3545083  | FEM 15-20       | 6418074035479 | M32      | 15-20             | 32,5 | 1-4   | 38,5  | 24,8 | 17,5  | 25       |
| 3545084  | FEM 19-28       | 6418074035486 | M40      | 19-28             | 40,5 | 1-4   | 48,5  | 30   | 20,4  | 25       |
| 3545085  | FEM 27-35       | 6418074035530 | M50      | 27-35             | 50,5 | 1-4   | 60,5  | 35   | 23,9  | 10       |
| 3545103  | FEM 34-45       | 6418074070852 | M63      | 34-45             | 63,5 | 1-4   | 73,5  | 40   | 28,9  | 5        |
| 3546151  | MFM 8-12        | 6418074036803 | M50      | 3x 6-10, 3x 10-14 | 50,5 | 2-6   | 58    | 20   | 9     | 1        |

