

Filter mat, Extract: W: 1180 mm, H: 55 mm, IP54,

Model	
product brand name	SIVACON
product designation	filter mat
type of ventilation	ventilation
fan design withdrawable fan	No
design of the product EMC version	No
General technical data	
cutout width	1 180 mm
cutout height	55 mm
Protection class	
protection class IP	IP54
Product details	
product component fan	No
Mechanical Design	
height	1 180 mm
width	55 mm
fastening method	Other
fastening method	
• 19-inch installation	No
• wall mounting	No
Net Weight	0.02 kg
material	plastic
ambient temperature during operation	
• minimum	-10 °C
• maximum	55 °C
Approvals Certificates	
General Product Ap- proval	other
Environment	



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6000-0AM42>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6000-0AM42>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6000-0AM42

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

