

260mm Table / Mitre Saw

LH1040

| | |
|-----------------|----------|
| Blade diameter | 260mm |
| Bore diameter | 30/25mm |
| Max mitre range | 45°-52° |
| Max bevel range | 45°-0° |
| Max table cut | 40mm |
| No load speed | 4,800rpm |
| Input wattage | 1,650w |
| Net weight | 14.3kg |

| Mitre Angle | Bevel Angle | |
|-------------|-------------|----------|
| | 45° (left) | 90° |
| 90° | 35x130mm | 69x130mm |
| 45° (left) | 35x65mm | 69x85mm |
| 52° (right) | 35x91mm | 69x85mm |



Recommended Blade: B-09020



LH1040

STANDARD EQUIPMENT: TCT blade, holder, triangular rule, push stick, socket wrench, dust bag.

255mm Mitre Saw

MLS100

| | |
|-----------------|--------------------|
| Blade diameter | 255mm |
| Bore diameter | 30mm |
| Max mitre range | 45° left and right |
| No load speed | 4,200rpm |
| Input wattage | 1,500w |
| Net weight | 14.7kg |

| Mitre Angle | Bevel Angle | |
|-------------|-------------|------------|
| | 90° | 45° (left) |
| 90° | 75x130mm | 75x120mm |
| 45° | 75x120mm | 45x90mm |



Recommended Blade: B-08888



MLS100

STANDARD EQUIPMENT: Blade, dust bag, holders, vertical vice, triangular rule, spanner.

260mm Mitre Saw

LS1040

| | |
|-----------------|----------|
| Blade diameter | 260mm |
| Bore diameter | 30/25mm |
| Max mitre range | 45°-52° |
| Input wattage | 1,650w |
| No load speed | 4,600rpm |
| Net weight | 12.4kg |

| Mitre Angle | Bevel Angle | |
|-----------------|-------------|-----------|
| | 45° (left) | 90° |
| 90° | 48x95mm | 90.5x95mm |
| | 35x130mm | 69x130mm |
| 45° | 48x67mm | 90.5x67mm |
| (left or right) | 35x92mm | 69x92mm |



Recommended Blade: B-08925



LS1040

STANDARD EQUIPMENT: Vertical vice, dust bag, holders, triangular rule.