

## Features

- Superimposable and stackable.
- These products are made from pre-consumer and post-consumer waste.
- Static load resistance: 50 kg (250 kg in stacked condition).
- Impact resistance: ~ 720 N (method EN 840-5 point 4.7.2).
- Working temperatures: from - 20 °C to +60 °C.
- External dimensions : 60x40x22 cm – capacity 42 liters

## RS PRO Storage Bins

RS Stock No.: 0625758



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

*These Euronorm plastic crates, in a large variety of sizes and options, are a standardized solution for storing, protecting and transporting goods suitable for warehouses, work stations, storerooms, assembly departments...*

*Upright lids are available separately. The peculiar feature of this range is the material, a recycled polypropylene coming from urban and industrial waste.*

## General Specifications

|                           |                                      |
|---------------------------|--------------------------------------|
| Type                      | Euronorm Crate                       |
| Portable                  | Yes                                  |
| Bin Material              | Recycled Plastic; PP (polypropylene) |
| Colour                    | Grey                                 |
| For Use With              |                                      |
| Total (NL) No. of Louvres |                                      |
| Capacity                  | 42 litres                            |
| Pack Quantity             | 1                                    |
| Finish                    |                                      |

| External dimensions |                   |
|---------------------|-------------------|
| Dimension           | 400 x 600 x 220mm |
| Overall Height      | 220mm             |
| Overall Width       | 400mm             |
| Overall Depth       | 600mm             |
| Overall Base Length |                   |

| Internal dimensions |                   |
|---------------------|-------------------|
| Dimension           | 365 x 565 x 215mm |
| Height              | 215mm             |
| Width               | 365mm             |

# Storage Bins



|             |       |
|-------------|-------|
| Depth       | 565mm |
| Base length |       |

## Approvals

|                           |             |
|---------------------------|-------------|
| Compliance/Certifications |             |
| Declarations              | REACH, RoHS |

