

Product type designation

Product description

Distance piece MDS D160 / MDS D460

Support for mounting transponders with 16 mm diameter and 10 mm distance to metal

MOBY D/RF300 ISO Spacer for MDS D160/MDS D460; Packing unit = Minimum order quantity: 50 units



Suitability for use

Support is mounted with an M4 countersunk head screw, the transponder is snapped on

Mechanical data

Material	PA 6.6 GF
Color	black

Ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during operation 	-25 ... +85 °C
<ul style="list-style-type: none"> during storage 	-25 ... +100 °C
<ul style="list-style-type: none"> during transport 	-25 ... +100 °C

Design, dimensions and weights

Height	14 mm
Diameter	20 mm

Further information / Internet-Links

Internet-Link

- to website: TIA Selection Tool
- to website: Selector SIMATIC NET SELECTION TOOL
- to the website: IWLAN
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

last modified:

<http://www.siemens.com/tia-selection-tool>

<https://support.industry.siemens.com/WW/view/en/67384964>

<http://www.siemens.com/iwlan>

<http://www.siemens.com/ident/rfid>

<https://mall.industry.siemens.com>

<http://www.siemens.com/industry/infocenter>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

05/08/2020