

PRODUCT-DETAILS

TY38MX

CABLE TIE 50LB 8IN BLK NYL PUSH MNT



General Information

Extended Product Type	TY38MX
Product ID	7TAG009530R0006
EAN	5414363064404
Catalog Description	CABLE TIE 50LB 8IN BLK NYL PUSH MNT
Long Description	Push Mount Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/215 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 185mm (7.3 Inches), Width of 4.8mm (0.19 Inches), Thickness of 1mm (0.04 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Bulk Pack

Ordering

EAN	5414363064404
UPC	786210770505

Dimensions

Product Net Width	0.184 in 4.67 mm
Product Net Depth / Length	7.88 in 200.2 mm

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	10 in 254 mm
Package Level 1 Height	5.75 in 146 mm
Package Level 1 Depth / Length	15.25 in 387 mm
Package Level 2 Units	104000 piece

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19750325
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000577
Instructions and Manuals	TY38MX

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5035 >> Push Mount Cable Ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

