



Outlet filter, Extract: W: 92 mm, H: 92 mm, RAL 7032, IP54,

Model		
product brand name	SIVACON	
product designation	outlet filter	
type of ventilation	ventilation	
fan design withdrawable fan	No	
design of the product EMC version	No	
General technical data		
cutout width	92 mm	
cutout height	92 mm	
Protection class		
protection class IP	IP54	
Appearance		
color	pebble grey	
Product details		
product component fan	No	
Mechanical Design		
height	105 mm	
width	105 mm	
depth	17 mm	
installation location	Control cabinet...panels, door	
fastening method	snap-on mounting	
fastening method • 19-inch installation • wall mounting	No Yes	
net weight	0.1 kg	
material	plastic	
ambient temperature during operation • minimum • maximum	-20 °C 65 °C	
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Miscellaneous](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6400-2GV10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6400-2GV10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6400-2GV10

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

