









Vertical mounting
OR within $\pm 60^\circ$ of vertical is recommended



Recommended
installation direction
建議安裝朝向

- Note:
- * $\varnothing$ Important Dimension.
 - * Waterproof Rate: IP68(2m/1h), IP69K.
 - * Body And Cap: Nylon+GF, Black.
 - * Membrane: ePTFE
 - * Filter: Sorbent
 - * Recommended installation length: $L > 15\text{mm}$
 - * Flame Retardant: UL94 V-0
 - * UV Resistance: UL746C F1
 - * Air Permeability: $> 1067\text{ml/min@7kPa}$.
 - * Temperature Resistance: $-40^\circ\text{C} \sim 150^\circ\text{C}$.
 - * All Parts Are RoHS Compliant.

UNIT: mm



TITLE
BREATHABLE VENT, PLASTIC, FIT IN

TOLERANCE
.X ± 0.25
.XX ± 0.1
.XXX ± 0.05
ANGLES $\pm 1^\circ$

SCALE 3:2
SIZE A4
SHEET 2 OF 2
REV. A
WC-REV. .0
QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO
VT-BPQ02BK-N08001

DRAWN BY
Henry

DATE
2025-03-12

DWG NO
VT-BPQ02BK-N08001

CHECKED BY
Jerry

DATE
2025-03-12

CUSTOMER
ALTW

APPROVED BY
Fred

DATE
2025-03-12

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.