



330 +2X100 Wood-Compo Tang Thru Screwdriver

Does not slip even when oily.



- Extraordinary non-slip grip; Secures working efficiency even with oily hands.
- Tang-thru type, which can be tapped by a hammer. With star-shaped nut.
- Rust-resistant black chrome plating shank.
- Wood-composite resin, reproducing the natural material texture.
- Only 3% less torque rate with slippery and oily hands compared to dry using
- High toughness shank made of fully hardened chrome vanadium steel.

PRODUCT SPECIFICATION

Index	Modèle	Product							Inner	Outer	EAN
			mm	mm	mm	mm	mm	mm	C/T	C/T	
120041	330 (-)5.5X75	Wood Compo Tang Thru Screwdriver -5.5x75	5.5	0.8	75	5.5	30	183	6	120	4907587074362
120042	330 (-)6X100	Wood Compo Tang Thru Screwdriver -6x100	6.0	0.9	100	6.4	32	217	6	120	4907587074379
120043	330 (-)6X150	Wood Compo Tang Thru Screwdriver -6x150	6.0	0.9	150	6.4	32	267	6	60	4907587074553
120044	330 (-)8X150	Wood Compo Tang Thru Screwdriver -8x150	8.0	1.1	150	8	35	277	6	60	4907587074386
120045	330 (+)1X75	Wood Compo Tang Thru Screwdriver PH1x75	PH1		75	5.5	30	183	6	120	4907587074393
120046	330 (+)2X100	Wood Compo Tang Thru Screwdriver PH2x100	PH2		100	6.4	32	217	6	120	4907587074409
120047	330 (+)2X150	Wood Compo Tang Thru Screwdriver PH2x150	PH2		150	6.4	32	267	6	60	4907587074560
120048	330 (+)3X150	Wood Compo Tang Thru Screwdriver PH3x150	PH3		150	8	35	277	6	60	4907587074416