

Eaton 12TKLEJ125

Catalog Number: 12TKLEJ125

Eaton Bussmann series medium voltage DIN fuse, 125 A, AC 12 kV, 3", 76 x 292 mm, backup, DIN, with striker

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage DIN fuse	12TKLEJ125
	EAN
	5027590326322
UPC	Product Length/Depth
051712186148	292 mm
Product Height	Product Width
80 mm	76 mm
Product Weight	Compliances
3500 g	DIN 43625
	VDE 0670-4
	IEC 60282-1
Certifications	
UL	
VDE	

Product specifications

Used with

270303 Fuse clip

A3354730 Fuse clip

Type

Fuse

Special features

Back-up, Transformer protection, Indoor or outdoor use

Application

transformer protection

indoor or outdoor use

Amperage Rating

125 A

Fuse indicator

With Striker

Fuse size

76 x 292 mm

Breaking capacity

63 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

DIN

Utilization category

Other

Voltage type

Resources

Technical data sheets

[720105 17.5kV DIN medium voltage fuses](#)

[720104 12kV DIN medium voltage fuses](#)

[720106 24kV DIN medium voltage fuses](#)

AC

With striker

Yes

Class

Class back-up

Barrels

1

Construction type

Bolt-on

Pre arc (I²T)

4 x 10000

Resistance

3.99 Ohms

Watt losses

93 W

Fuse diameter

76 mm

Color

Brown

Interrupt rating

63 kAIC

Construction size

76 x 292 mm

Mounting method

Clip-in

Packaging type

Standard

Quantity

1

Voltage rating

12 kV

Fuse type

TKLEJ



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia