

FEATURES

- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight exposure
- **High Tensile Strength:** Withstands up to 34 kg, ensuring reliable cable bundling
- **UL 94 V-2 Fire Behaviour:** Meets safety standards for flammability, enhancing safety in critical applications
- **Maximum Bundle Diameter of 70 mm:** Accommodates a wide range of cable sizes
- **Temperature Range up to 85 °C:** Suitable for use in high-temperature environments
- **4.8 mm Width:** Provides a balance of strength and flexibility

RS PRO 280mm Nylon Cable Tie, Non-Releasable

RS Stock No: 656-058



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO cable ties are designed for securing and organising cables efficiently. Made from durable nylon, they are ideal for bundling cables in a variety of environments. The non-releasable design ensures a secure hold, making them perfect for permanent installations.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	34 kg

Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

Mechanical Specifications

Length	280 mm
Material	Nylon
Maximum Bundle Diameter	70 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---