

## Han EMC/B 16B CP f SL



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 816 5406
Specification	Han EMC/B 16B CP f SL
HARTING eCatalogue	<a href="https://harting.com/09628165406">https://harting.com/09628165406</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> EMC/B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings

### Version

Size	16 B
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP66

### Material properties

Material (hood/housing)	Polycarbonate (PC)
Colour (hood/housing)	Grey
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	60b1a572-bb3f-476f-9307-b7d1688bd90c
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	28.9 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140570580
eCl@ss	27440208 Cap for industrial connectors
UNSPSC 24.0	39121467