



Features

• SylWork offers a range of high-performance LED work lights, available in both mains-powered and battery-operated models. Designed for ultimate flexibility, SylWork provides reliable, temporary lighting for a variety of DIY projects, including home decorating, household repairs, cleaning, tidying, and general maintenance tasks. The SylWork Head Lamp is a rechargeable, battery-operated headlamp designed for DIY projects, maintenance work, camping, and outdoor activities. With an output of up to 100 lumens and six different lighting modes, it adapts to various needs. It also features a Flashlight Mode, emitting a blinking red and green light for emergencies, ensuring visibility when it matters most. Producing a crisp 10,000K frost white light, it delivers exceptional brightness for any task. Built for durability and practicality, it fully charges in just four hours and includes a three-year warranty for long-term reliability.

Product Overview

Product name	SylWork Headlamp
Technology	LED
Cap/Base	N/A
Housing	ABS Plastic
Mount	Other
General application	Residential & Consumer
ETIM Class	EC000347
Fixture luminous flux (lm)	30
Correlated colour temperature (k)	10000
Light colour	Daylight
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam Angle (°)	60
Photobiological Risk Group	RG1



SylWork Headlamp
0090203

Total power consumption (W)	3
Electrical protection	Class III
Control gear type	Not required
Dimmable	No
Housing colour	Black
IP rating	IP54
IK rating	IK03
Product EAN number	5410288902036
Warranty	3 years
Dimming method	N/A

Data table

GENERAL DATA	
Product name	SylWork Headlamp
Technology	LED
Cap/Base	N/A
Housing	ABS Plastic
Mount	Other
General application	Residential & Consumer
Operating temperature range (°C)	-10°C...+40°C
ETIM Class	EC000347
Warranty	3 years
OPTICAL DATA	
Fixture luminous flux (lm)	30
Correlated colour temperature (k)	10000
Light colour	Daylight
CRI (Ra)	80
Colour Variation Initial (SDCM)	6
Beam Angle (°)	60
Distribution type	None
Photobiological Risk Group	RG1

ELECTRICAL DATA

Total power consumption (W)	3
Electrical protection	Class III
Control gear required	No
Control gear type	Not required
Dimmable	No
Dimming method	N/A
Energy Efficiency Class (A->G) of contained light source	G, G(more than 1 Light Source)
Nominal Frequency (Hz)	DC

LIFETIME DATA

Lifespan L70 B50	25000
------------------	-------

PHYSICAL DATA

Housing colour	Black
IP rating	IP54
IK rating	IK03
Diffuser finish	Transparent
Diffuser material	PC Polycarbonate
Reflector finish	Not Applicable
Nominal Product Length (mm)	63.5
Nominal Product Width (mm)	40
Nominal Product Height (mm)	46.5
Weight (kg)	0.074

PACKAGING

Product EAN number	5410288902036
Packaging single length / height (cm)	6.0
Packaging single width (cm)	8.0
Packaging single depth (cm)	5.5
DUN14 (inner)	15410288902033
Units per outer package	80



SylWork Headlamp
0090203

Packaging outer length / height (cm)	38.0
Packaging outer width (cm)	33.0
Packaging outer depth (cm)	27.5

SAFETY DATA

Glow Wire Test (°C)	650
Optimal operating condition (°C)	-10-40
Special purpose lamp	No
Dry applications use only	No
Suitable for household illumination	No