



# Product data sheet

Power tools for trade & industry

Digital Inclinometer

## PRO GIM 60 L



Laser-accurate incline transfer over longer distances

### The most important data

Length	60 cm
Measurement range	0° – 360° (4 x 90°)
Electronics measurement accuracy 0°/90°	± 0.05°

**Order number** 0 601 076 900

## Technical data

### Additional data

Length	60 cm
Measurement range	0° – 360° (4 x 90°)
Electronics measurement accuracy 0°/90°	± 0.05°
Electronics measuring accuracy at 1– 89°	± 0.1°
Working range (laser)	30 m
Power supply, inclination measurement	1 x 9 V-6LR61 + 2 x 1.5 V LR03
Weight approx.	0.91 kg
Laser type	650 nm, < 1 mW
Laser range	30 m
Laser class	2
Levelling accuracy of laser	± 0.5 mm/m
Units of measurement	°, %, mm/m
Tripod thread	1/4"



**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

---

## Advantages:

- Integrated point laser for incline measurement up to a distance of 30 m
- Strong magnets and two straps for securely fastening the instrument to workpieces
- Incline mechanism for fine adjustment on uneven surfaces



---

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/mz/en/wac/>

