



cubio maintenance trolley with cupboard / 4 drawers & lino top (525/525). Featuring a heavy duty, reinforced steel housing with double, independent, storage sections, push - pull handle, 100% extension drawers with drawer blocking and 125mm diameter castors. Drawer configuration: 1x 100mm, 2x 150mm, 1x 200mm (50kg U.D.L.) and cupboard section with single, perfo lined door and 1 galvanised steel shelf (100kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 7035 light grey. WxDxH: 1050x525x890mm

Breite [mm]: 1050
Tiefe [mm]: 525
Höhe [mm]: 890
Bruttogewicht [kg]: 102.91
EAN-Code: 5039350086858
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Light grey
Main RAL colour	RAL 7035
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	cubio
---------------	-------

Schubladen

Number of drawers	4
Drawer load capacity [kg]	50
Drawer height 1 [mm]	100
Drawer height 2 [mm]	150

Drawer height 3 [mm]	150
Drawer height 4 [mm]	200

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Lino
Shelf load capacity [kg]	100
Door type	Perfo
Door height 1 [mm]	700