

Article No. : 1FL2306-1AC01-0MB0



Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

| Basic motor data        |                                    |
|-------------------------|------------------------------------|
| Motor type              | Permanent-magnet synchronous motor |
| Motor type              | High Inertia                       |
| Static torque           | 3.70 Nm                            |
| Static current          | 2.50 A                             |
| Maximum torque          | 12.00 Nm                           |
| Maximum current         | 8.4 A                              |
| Maximum speed           | 3,000 rpm                          |
| Rotor moment of inertia | 7.9600 kgcm <sup>2</sup>           |
| Weight                  | 5.9 kg                             |

| Rated data                        |           |
|-----------------------------------|-----------|
| SINAMICS S200, 3 AC 380 ... 480 V |           |
| Rated speed                       | 2,000 rpm |
| Rated torque                      | 3.58 Nm   |
| Rated current                     | 2.5 A     |
| Rated power                       | 0.75 kW   |

| Encoder system |                                                       |
|----------------|-------------------------------------------------------|
| Encoder system | Absolute encoder 21-bit singleturn + 12-bit multiturn |

| Motor connection |                         |
|------------------|-------------------------|
| Connection type  | Metal angular connector |

| Mechanical data               |                      |
|-------------------------------|----------------------|
| Design acc. to Code I         | IM B5 (IM V1, IM V3) |
| Vibration severity grade      | Grade A              |
| Shaft height                  | 65                   |
| Flange size (AB)              | 130 mm               |
| Centering ring (N)            | 110 mm               |
| Hole circle (M)               | 145 mm               |
| Screw-on hole (S)             | 9.0 mm               |
| Overall length (LB)           | 148.2 mm             |
| Diameter of shaft (D)         | 22 mm                |
| Length of shaft (E)           | 58 mm                |
| Length of flange diagonal (P) | 165.2 mm             |
| Shaft end                     | Plain shaft          |
| Color of the housing          | Anthracite RAL 7016  |

