



ENGLISH

Datasheet

Line Mounting Hydraulic Flow Control Valve, G 1/4, 700 bar

RS Stock number 2975883



Features

Materials:

Body: Steel 9SMn28K or 316 Stainless Steel

Stem: 316 Stainless Steel

Stem Seal: PTFE

Temp Range: -20 to +240° C

Control: Tee Bar - 316 Stainless Steel

Connection: BSPP - BSPT- NPT

Female x Female (Male x Female available)