

CHERRY 



**Smart Terminal
ST-1144**

DATASHEET

CHERRY Smart Terminal ST-1144

USB SMART CARD TERMINAL - DURABLE AND SMART

Smart, stable, energy-saving and can be operated with one hand. Whether access controls, network logon or chipcard-based transactions – the ST 1144 supports you in protecting your sensitive data in a simple and easy way.

Smart, stable and can be operated with one hand. The SmartTerminal ST-1144 reads and writes your chipcards - and with extremely low power consumption to boot. Whether access controls, network logon or smart card-based Internet transactions - the SmartTerminal with USB connection supports you in protecting your sensitive data in an easy and reliable way.



HIGHLIGHTS

- High-quality USB-smartcard reader
- OmniKey 3121 (Aviator) compatible
- USB 2.0-compatible
- Weighted base for "single-handed operation"
- PC/SC smartcard reader
- Protocols: T=0, T=1, S=8, S=9, S=10
- CCID compatible
- EMVco Level 1 compliant
- CAC and FIPS 201 compliant
- TAA compliant

SCOPE OF DELIVERY

- Manual
- Smartcard Terminal

TECHNICAL DATA

PRODUCT INFORMATION

Model number	ST-1144
Reliability	MTBF > 45.000 hours
Warranty	3 years warranty
Product approvals	<ul style="list-style-type: none">- cURus- GS- VCCI- CE- FCC- UKCA
Software support	<ul style="list-style-type: none">- Card Reader Tools- PC/SC Diagnose Tool
System Requirements-Hardware	USB-A

TEMPERATURE

Min. operating temperature	0 °C
Max. operating temperature	60 °C

PRODUCT VARIANTS

PART NUMBER

COLOUR

ST-1144UB

black/grey

SMART TERMINAL 1144 [ST-1144UB]



Product colour: Grey

Part number	ST-1144UB
EAN	4025112086892
UPC	840183605582

PRODUCT INFORMATION

Model number	ST-1144
Reliability	MTBF > 45.000 hours
Warranty	3 years warranty
Product approvals	<ul style="list-style-type: none">- cURus- GS- VCCI- CE- FCC- UKCA
Software support	<ul style="list-style-type: none">- Card Reader Tools- PC/SC Diagnose Tool
System Requirements-Hardware	USB-A
Dimensions inc. packaging	150 mm × 120 mm × 60 mm 374 g

TEMPERATURE

Min. operating temperature	0 °C
Max. operating temperature	60 °C

© Cherry Europe GmbH

Cherrystraße 2 · 91275 Auerbach/OPf. · Germany
cherry-world.com · cherry.de

Sales Support · Technischer Support · eHealth Support

+49 9643 - 2061 - 100
www.cherry.de/de-de/kontakt

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.