

Features

- Recycling of condensing water improves cooling efficiency
- Automatic diagnosis & over-cold prevention function
- Dual motor setup constitutes dust heatexchanging system
- New refrigerant R290, more environmentally friendly & F-gas quota free
- Programmable 24hours timer
- Sleep function
- 3 fan speed
- Auto swing function
- With handle design easy to move
- Remote control
- 4 modes:
 - Cool Mode
 - Dehumidifer Mode
 - Fan Mode
 - Auto Mode

RS PRO 10000 BTU/H 4-in-1 Portable Air Conditioning Unit, Type F Schuko Plug, Type G British 3 pin

RS Stock No.: 0732102



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO 4-in-1 Portable Air Conditioner, 10000BTU

RS PRO 4-in-1 Air Conditioner is perfect for indoor applications and packed with impressive operational features and modes. Upon inspection, this unit is sleek and portable. The unit has 10,000BTU cooling capacity and include 4-in-1 modes for Cool, Dehumidifier, Fan and Auto. This air conditioning unit can be placed discretely in the desired location, controlled remotely, and will not spoil the ambiance that has been created.

The RS PRO air conditioning unit is ideal for domestic and commercial use ensuring personnel can work and relax in relative comfort. This cost-effective unit puts you in control manually or remotely, offers handles for portability, and is brilliant at heating, cooling, and dehumidifying the air.

FEATURES & BENEFITS

- *Cool Mode offers an adjustable target temperature down to 15°C (10,000BTU / 4kW).*
- *Dehumidifier Mode removes moisture from the air with max. capacity of 1.0ltr/hr (external collection required).*
- *Fan Mode operates as a 3-speed cooling fan without engaging the climate control functions.*
- *Auto Mode engages the internal temperature sensor to initiate either the cool or fan modes based on the temperature parameters set by the user.*
- *Auto Swing Function*
- *A timer, sleep mode and child lock function*
- *The remote control provides additional user convenience.*
- *Castor design allows the unit to be easily moved and positioned between locations for use.*
- *LED display indicates room temperature and is visible at night or darkened rooms.*

General Specifications

Cooling Capacity	10000Btu/h
Unit Type	Portable Air Conditioning Unit
Air Flow	380m ³ /h
Refrigerant Type	R290
Plug Type	Type F – Schuko plug, Type G – British 3-pin
Supply Voltage	230V ac
Input Power Rating	1110W
Dimensions	330 x 315 x 700mm
Mounting	Portable
Depth	315mm
Height	700mm
Width	330mm

Mechanical Specifications

Cooling Capacity	2900W
Rating Input (Cooling)	1110 W
Moisture Removed	1.0L/H
Working Area	18m ³
Noise Level (High)	<65 dBA
Length of Power Cord (exposed)	1.8 meters
Product Weight (G.W)	23.5kg

Approvals

Declarations	REACH DoC
Certificate	CE, GS, VDE
Standards Met	EN60335-2-40:2003+A11:2004+A12:2005+A1:2006+A2:2009+A13:2012 EN60335-1:2012+A11:2014+A13:2017+A1:2019+A14:2019+A2:2019 EN62233:2008 AfPS GS2019:01 PAK

Similar Products

Stock No.	Brand	Product Name	Cooling Capacity	Air Flow	Water Tank Capacity	Moisture Removed
231-1513	RS PRO	Portable Air Conditioner	18000Btu/h	680m ³ /h	N/A	2.2L/H
187-5321	RS PRO	Portable Air Conditioner	15000Btu/h	690m ³ /h	3L	1.8L/H
5320	PRO	Portable Air Conditioner	13000Btu/h	430m ³ /h	2.5L	1.5L/H
231-1513	RS PRO	Portable Air Conditioner	11500Btu/h	410m ³ /h	3.5L	1.0 L/H
XXX-XXXX A027L-14C	RS PRO	Portable Air Conditioner	14000Btu/h	320m ³ /h	N/A	1.7L/H
XXX-XXXX FGA-1096F	RS PRO	Portable Air Conditioner	10000Btu/h	380m ³ /h	N/A	1L/H

Electrical Specifications

