

XCKD2145N12

Limit Switch , Adjustable Lever Arm with Thermoplastic Roller (ZCY45)



List Price \$94.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Actuation	CW and CCW
Actuator Action	Momentary
Actuator	Adjustable Lever Arm with Thermoplastic Roller (ZCY45)
Head Type	Rotary (ZCE01)
Roller Dimension	16 x 5.5mm
Operating Torque/Force	14.16 Inch-Ounces (0.10Nm)
Marketing Trade Name	OsiSense
Lever Arm Length	33 to 83.5mm
Maximum Actuation Speed	1.5 m/s
Type	XCKD
RoHS	Yes
Body Type	Compact Modular (ZCD21)
Type of Duty	General Duty
Shock Resistance	50G
Vibration Resistance	25G
Body Material	Metal
Connection Type	Conduit Entrance (0.5" NPT)
Contact Configuration	1 N.O./1 N.C.
Weight	0.518 lbs (0.235kg)
Contact Operation	Snap Action
Positive Opening	Yes
Terminal Type	Screw Clamp
Ampere Rating	10A
Maximum Voltage Rating	240VAC/250VDC
NEMA Enclosure Rating	NEMA 1/2/4/6/12/13
Degree of Protection	IP66/67
Operating Temperature Range	-13 to 158°F (-25 to 70°C)
Approvals	UL Listed - CSA Certified - CE Marked
Conforming to Standards	CENELEC EN 50047

Shipping and Ordering

Category	22418 - Limit Switches, Medium Duty, Compact, IEC, Type XCKP & XCKT
Discount Schedule	T
GTIN	00785901300489
Package Quantity	1
Weight	0.48 lbs.

Generated: 07/13/2010 15:59:58

Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.