

Features

- Spotlight & floodlight modes
- Compact pocket size
- Strong magnetic base
- Useful pocket clip
- USB-C rechargeable

RS PRO LED Torch Black, Rechargeable 1000 lumen, 125mm

RS Stock No.: 0143262



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Rechargeable Aluminium Torch

Spotlight/Flashlight - 1000 Lumen (plus Turbo: 2000LM)
 Additional strip of floodlight SMD LEDs - 500 Lumen
 1x2000mAh 18650 li-ion battery included
 With metal pocket clip & magnetic base
 USB Type-C 5V-1A charging - cable included
 With battery level and charging indicator under switch
 Charge time approx. 6 hrs
 IPX4 water resistant

General Specifications

Torch Style	Torch
Rechargeable	Yes
Plug Type	USB
Lamp Type	LED
Luminosity	1000 lm, plus 2000lm boost
Case Material	Aluminium
Batteries	Li-Ion
Beam Type	Spot and flood beams
Water Resistant	Yes, IPX4 water resistant
Length	125 mm
Colour	Black, Red

Mechanical Specifications

USB	Type-C 5V 1A charging
Battery Charge Time	6 hours
Battery	3.7v 18650 2000mAh Li-ion battery
Dimensions	125 x 26 x 31 mm
Weight	140g
Operation	<p>Switch Modes: Spotlight high - 1000LM - 2.5hrs > Spotlight Low - 200LM - 6hrs > Strobe > Off</p> <p>Double click to enter Flood modes: COB High - 500LM - 3hrs > COB Low - 100LM - 9hrs > OFF</p> <p>Press and Hold switch at any time to enter Spotlight 2000LM Turbo mode – lasts 30 seconds</p>

Approvals

Declarations	<p>EMC</p> <p>RoHS</p> <p>REACH</p>
Standards Met	<p>EN IEC 55015:2019+A11:2020</p> <p>EN 61547:2009</p> <p>IEC 62321</p> <p>IPX4</p> <p>IEC 62133</p>