

DUNA LOW

S1PS FO SR

FT7 1170 BI2 01



SPECIFICATIONS

Upper	highly breathable suede leather upper
Lining	BI-FRESH PLUS 3D lining with high breathability and top abrasion resistant
Toe-cap	aluminium BI-ALLOY
Nail protection	Zero Perforation fabric PS BI-SAFE metal-free
Sole	Bi-density PU with BI-SHANK arch support
Insole	DAMPER PRO
Sizes	36/42
Fit	Mondopoint 11
Safety Norms	EN ISO 20345:2022
Weight (Size 42)	570g

WORK ENVIRONMENTS

Automotive / Logistics / Agriculture / Craftmanship / Precious metal / Light Industry / Engineering / Mechatronics / Warehousing



DESCRIPTION

DUNA LOW is a sporty safety shoe in S1PS protection class with highly breathable suede leather upper

TOE-CAP



COMPONENTS

DAMPER PRO: New insole in open-cell PU with antibacterial fabric, shaped and anatomical, it is designed to increase comfort, shock absorption, especially in the heel area, improving the discharge of energy accumulated while walking and moving weights

INSOLE



BI-ALLOY: New ultra-light and non-magnetic toe cap, made with approximately 56% recycled aluminum. The special production system makes it extremely reliable even in the most critical situations. The toe-protection band makes it very comfortable.

STANDARD LABEL



PLUS

BI-FRESH PLUS: Three-dimensional Polyester lining with high abrasion resistance and breathability


 Calzaturificio 5BI S.r.l.
 Via Trani, 94-100
 76121 Barletta (BT)

BI-SHANK: is the new system designed to stabilize the sole by counteracting longitudinal imbalances and facilitating the natural walking motion.



FT7 1170 BI2 01

42

bicap.it

S1PS FO SR



Year and month of manufacture

Lot / Batch Number

EN ISO 20345:2022



do not re-use