



CAR-HGV INFLATOR, ŃEURODAINUÎ MODEL **RC1855E**

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:16





DESCRIPTION

CAR-HGV INFLATOR, ŃURODAINUŃ MODEL

Conform to Standard EEC No 217
Coupling pipe length: 400 mm.
Nickel-plated aluminium body.
Supply pressure: 0-12 bar.
Protected \varnothing 60 mm pressure gauge. 0-10 bar.
Standard coupling 25/w standardised + Quick connection coupling.
MICHELIN-approved.

STANDARDS / DIRECTIVES

86/217/CE, NFR 63-302

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:16



SPECIFIC DATA

Designation	EURODAINU MICHELIN INFLATING GUN
Sales reference	RC1855E
L (mm)	
Weight (g)	810
l (mm)	
h (mm)	
C mm	0 - 12
C mm	1/4"
Inner pipe diameter mm	0.4
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:16

