



Datasheet 183-4226

RS PRO UNCOATED BALL-LOCK STAINLESS STEEL CABLE TIES

EN



Technical Information:

Material: Stainless Steel Grade 304

304 grade stainless steel, for standard applications

Working Temp.: -80°C to +500°C

Description: Metallic band and buckle

Flammability: Fireproof

Other Properties: UV-resistant

Product Feature: Uncoated version, for high temperature applications, quick installation.

Applications: Ideal for petrochemical, food industry, industries, power stations, mining, ship-building, offshore and any other aggressive environments.

Specification

RS CODE	EASE CODE	LENGTH		WIDTH		TICKNESS		MAX. BUNDLE DIAMETER		MIN. TENSILE STRENGTH	
		mm	inch	mm	inch	mm	inch	mm	inch	N	lbs
1834223	CT-SS-BL125/4.6UC-304	125	4.9	4.6	0.18	0.26	0.010	31	1.23	1100	250
1834224	CT-SS-BL-200/4.6UC-304	200	7.9					50	1.97		
1834225	CT-SS-BL-360/4.6UC-304	360	14.2					90	3.55		
1834226	CT-SS-BL-360/7.9UC-304	360	14.2	7.9	0.31	0.26	0.010	90	3.55	1500	340

