

## Features

- Designed for versatility across a wide range of metal cutting applications.
- Delivers consistent performance when working with regular-strength steel.
- 1.4mm tooth pitch ensures clean, accurate cuts in pipes and profiles ranging from 1.5–4.0mm.
- 150mm blade length provides a cutting capacity of up to 100mm.

## Reciprocating Saw Blade - Metal 150 x 19 x 0.9mm –Precision Cut

RS Stock No.: 0757825



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Reciprocating Saw Blade

0757825 Metal Reciprocating Saw Blade is designed for versatility across a wide range of metal cutting applications. Manufactured from premium quality High Speed Steel for maximum durability and extended blade life, it delivers consistent performance when working with regular-strength steel. A fine 1.4mm tooth pitch ensures clean, accurate cuts in pipes and profiles ranging from 1.5–4.0mm, while the 150mm blade length provides a cutting capacity of up to 100mm.

- *Manufactured with 6150 Chromium-Vanadium Spring Steel & M2 High Speed Steel Teeth*
- *Universal Fitting, compatible with all S-shank 1/2" Reciprocating Saws*
- *Suitable for use on Sheet Metal, Pipes, Profiles and Box Section*
- *Supplied in 5pc Packs*

## General Specifications

<b>Tooth Design</b>	Side Set, Milled
<b>Type</b>	Reciprocating Saw Blade
<b>Teeth Spacing</b>	1.4mm
<b>TPI</b>	18
<b>Thickness</b>	0.9mm
<b>Max Cut Depth</b>	100mm
<b>Cut Type</b>	Precision Cutting
<b>Blade Material</b>	M2 High Speed Steel
<b>Body Material</b>	6150 Chromium-Vanadium Spring Steel
<b>Fitting</b>	S-Shank 1/2"
<b>Length</b>	150mm
<b>Width</b>	19mm

Stock No.	Cut Type	Thickness	Length	Width
XXX-XXXX 0757823	Progressive Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757824	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757825	Precision Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757826	Fine Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757827	Fast Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757828	Precision Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757830	Fine Cutting	0.9mm	225mm	19mm

## Approvals

<b>Declarations</b>	REACH DoC
---------------------	-----------

## Similar Products

Stock No.	Brand	Product Name	Cut Type	Thickness	Length	Width
XXX-XXXX 0757823	RS PRO	Reciprocating Saw Blade	Progressive Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757824	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757825	RS PRO	Reciprocating Saw Blade	Precision Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757826	RS PRO	Reciprocating Saw Blade	Fine Cutting	0.9mm	150mm	19mm
XXX-XXXX 0757827	RS PRO	Reciprocating Saw Blade	Fast Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757828	RS PRO	Reciprocating Saw Blade	Precision Cutting	0.9mm	225mm	19mm
XXX-XXXX 0757830	RS PRO	Reciprocating Saw Blade	Fine Cutting	0.9mm	225mm	19mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories