



Main

Range	Exiway
Product name	Exiway Easyled
Product or component type	Emergency light fitting
Device application	Lighting
Function	Standard
Supply	Maintained Non-maintained
Number of batteries	1 x 3.6 V 1.6 Ah Ni-Cd (Nickel-Cadmium)
Colour	White
Light source	LED integral LED 8 W
Light source colour	White
Cover type	Transparent
Wiring device additional information	Can be inhibited with rest mode via Teleur range of remote controls

Complementary

Range compatibility	Remote control
[Ue] rated operational voltage	220...230 V AC 50/60 Hz
Power consumption in VA	3.8 VA non-maintained 5.9 VA maintained
Power consumption in W	0.8 W non-maintained 2.6 W maintained
Current consumption	16 mA
Electrical insulation class	Class II
Autonomy	1 h
Charging time	12 H
Luminous flux	Emergency condition: 170 lm Maintained mode: 85 lm
Type of glass	Serigraphed transparent glass
Material	Housing: plastic Cover: plastic
Device mounting	Surface ceiling Flush false ceiling Flush wall Surface wall
Height	116 Mm
Width	292 Mm
Depth	37 Mm
Net weight	0.53 Kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

IP degree of protection	IP65
IK degree of protection	IK07
Ambient air temperature for operation	0...40 °C
Fire resistance	850 °C
Product certifications	ENEC
Standards	EN/IEC 60598-2-22 IEC 60695-2-10

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	535 G
Package 1 Height	4.4 Cm
Package 1 width	12.5 Cm
Package 1 Length	30.5 Cm
Unit Type of Package 2	S03
Number of Units in Package 2	12
Package 2 Weight	6.907 Kg
Package 2 Height	30 Cm
Package 2 width	30 Cm
Package 2 Length	40 Cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**