



ENGLISH

Datasheet

Stock No: 534-648

RS Pro Butt Wire Splice Connector, Blue, Insulated, Tin Plated 16 → 14 AWG



Product Details

RS Insulated Crimp Butt Splice Terminals

A range of insulated crimp butt splice terminals made from copper with flared vinyl or nylon (mini-yellow) insulation. These insulated crimp butt splice wire connectors are colour coded for use with different wire sizes including Mini Yellow 0.2 - 0.5 mm² (stock number 239-4234)

Mini Yellow 0.2 - 0.5 mm²

Red 0.5 - 1.0 mm²

Blue 1.5 - 2.5 mm²

Yellow 2.5 - 6.5 mm²

RS Pro Range

Conversion table	
M3 / 6 BA	M5/ 2BA
M3.5/ 4BA	M6/ 0BA
M4/ 3BA	

Wire Sizes	
Mini Yellow	0.2 - 0.5 mm ²
Red	0.5 - 1.5 mm ²
Blue	1.5 - 2.5 mm ²
Yellow	2.5 - 6.5 mm ²

Technical Specification	
Temperature rating	+70°C
Body Material	Copper
Body Plating	Tin



ENGLISH

Specifications:

Splice Type	Butt
Wire Size	16 → 14 AWG
Overall Length	24.5mm
Diameter	4.8mm
Insulation	Insulated
Colour	Blue
Insulation Material	PVC
Contact Material	Copper
Contact Plating	Tin