



ENGLISH

Datasheet

Stock No: 299-3875

RS Pro Pneumatic Elbow Tube-to-Tube Adapter, Push In Connection A 8mm, B 8mm



Product Details

Equal Elbow Tube-to-Tube Adaptor

Threaded, Tube-to-Tube & Adaptors

Threaded Tube-to-Tube & Adaptors

The push-on and screw collar design of these fittings makes them secure and suitable for instrumentation, vacuum and general purpose applications, and they can be used with nylon or polyurethane tubing.

Operating Temperature Range -18 to +70°C

Operating Pressure of -1 to 15 bar

Specifications:

Manufacturer Series	1130
Tube Connection A	Push In 8 mm
Tube Connection B	Push In 8 mm
Body Material	Stainless Steel
Maximum Operating Pressure	15 bar
Tube Connection A - Type	Push In
Tube Connection B - Tube Size	8mm
Tube Connection B - Type	Push In
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-18°C
Tube Connection A - Tube Size	8mm
Connection Style	Tube-to-Tube
