



Quality Products. Service Excellence.

Steel Chassis 1441 Series

Powder Coated, Real Walnut Side Option



Key Features:

- Spot welded steel - heavy duty construction chassis.
- Finished in ASA 61 smooth grey or satin black powder paint.
- Optional bottom plates are punched with 4 holes – 3/16” diameter (Chassis now includes 1/8” holes to allow installation of optional bottom plates).
- Hardware not provided, please order separately - Part number **1421J6** (Pkg. of 6, 6-32 Philips head screws).
- Rubber feet sold separately
- Some models accept chassis covers (1451 series)
- UPGRADE to our Satin Black Chassis with Walnut Sides (available for some sizes, refer to table below)



Photo Features:



Chassis available in black or gray.

Six models available with walnut sides (see table below for compatibility).



Perforated covers for most sizes. Bottom panels available for all sizes (sold separately from chassis).

Accessories

- Sheet Metal Screws

Chassis

| Gray Chassis | Satin Black Chassis | Satin Black Chassis w/ Walnut Sides | Steel Gauge | Width | Depth | Height | Gray Bottom Panel | Satin Black Bottom Panel | Gray Perforated Chassis Cover | Satin Black Perforated Chassis Cover |
|--------------|---------------------|-------------------------------------|-------------|-------|-------|--------|-------------------|--------------------------|-------------------------------|--------------------------------------|
| 1441-6 | 1441-6BK3 | | 20 | 4.00 | 4.00 | 2.00 | 1431-6 | 1431-6BK3 | | |
| 1441-8 | 1441-8BK3 | | 20 | 6.00 | 4.00 | 2.00 | 1431-8 | 1431-8BK3 | | |
| 1441-12 | 1441-12BK3 | 1441-12BK3CWW | 20 | 7.00 | 5.00 | 2.00 | 1431-12 | 1431-12BK3 | | |
| 1441-9 | 1441-9BK3 | | 20 | 8.00 | 4.00 | 1.00 | 1431-10 | 1431-10BK3 | 1451-10 | 1451-10BK3 |
| 1441-10 | 1441-10BK3 | | 20 | 8.00 | 4.00 | 2.00 | 1431-10 | 1431-10BK3 | 1451-10 | 1451-10BK3 |
| 1441-14 | 1441-14BK3 | | 20 | 9.00 | 5.00 | 2.00 | 1431-14 | 1431-14BK3 | 1451-14 | 1451-14BK3 |
| 1441-15 | 1441-15BK3 | | 20 | 10.00 | 6.00 | 1.00 | 1431-16 | 1431-16BK3 | 1451-16 | 1451-16BK3 |
| 1441-16 | 1441-16BK3 | 1441-16BK3CWW | 20 | 10.00 | 6.00 | 2.00 | 1431-16 | 1431-16BK3 | 1451-16 | 1451-16BK3 |
| 1441-22 | 1441-22BK3 | 1441-22BK3CWW | 20 | 12.00 | 8.00 | 2.00 | 1431-22 | 1431-22BK3 | 1451-22 | 1451-22BK3 |
| 1441-24 | 1441-24BK3 | 1441-24BK3CWW | 20 | 12.00 | 8.00 | 3.00 | 1431-22 | 1431-22BK3 | 1451-22 | 1451-22BK3 |
| 1441-29 | 1441-29BK3 | | 20 | 12.00 | 10.00 | 2.00 | 1431-29 | 1431-29BK3 | 1451-29 | 1451-29BK3 |
| 1441-18 | 1441-18BK3 | | 20 | 13.50 | 5.00 | 2.00 | 1431-18 | 1431-18BK3 | | |
| 1441-26 | 1441-26BK3 | | 20 | 16.00 | 8.00 | 2.00 | 1431-26 | 1431-26BK3 | 1451-26 | 1451-26BK3 |
| 1441-28 | 1441-28BK3 | | 20 | 16.00 | 8.00 | 3.00 | 1431-26 | 1431-26BK3 | 1451-26 | 1451-26BK3 |
| 1441-20 | 1441-20BK3 | | 20 | 17.00 | 4.00 | 3.00 | 1431-20 | 1431-20BK3 | | |
| 1441-30 | 1441-30BK3 | | 20 | 17.00 | 10.00 | 2.00 | 1431-30 | 1431-30BK3 | 1451-30 | 1451-30BK3 |
| 1441-32 | 1441-32BK3 | 1441-32BK3CWW | 20 | 17.00 | 10.00 | 3.00 | 1431-30 | 1431-30BK3 | 1451-30 | 1451-30BK3 |
| 1441-33 | 1441-33BK3 | 1441-33BK3CWW | 20 | 17.00 | 10.00 | 4.00 | 1431-30 | 1431-30BK3 | 1451-30 | 1451-30BK3 |
| 1441-34 | 1441-34BK3 | | 18 | 17.00 | 12.00 | 2.00 | 1431-34 | 1431-34BK3 | | |
| 1441-36 | 1441-36BK3 | | 18 | 17.00 | 12.00 | 3.00 | 1431-34 | 1431-34BK3 | | |
| 1441-38 | 1441-38BK3 | | 18 | 17.00 | 14.00 | 3.00 | 1431-38 | 1431-38BK3 | | |
| 1441-40 | 1441-40BK3 | | 18 | 17.00 | 14.00 | 4.00 | 1431-38 | 1431-38BK3 | | |
| 1441-42 | 1441-42BK3 | | 18 | 17.00 | 14.00 | 5.00 | 1431-38 | 1431-38BK3 | | |

Hardware

| Gray Chassis | Qty | Description | Note |
|--------------|-----|-------------|------|
|--------------|-----|-------------|------|

| Gray Chassis | Qty | Description | Note |
|--------------|-----|--|--|
| 1421J6 | 6 | 6-32 x 1/4" pan head, type C. screws | Use for attaching bottom plate to chassis |
| SC1440KT | 25 | #8 x 5/16" truss head screws and #8 serrated zinc plated lock washer | Use for attaching 1441 walnut sides (where applicable) |

Data subject to change without notice

© 2022. Hammond Manufacturing Ltd. All rights reserved.