

## Datasheet

# RS LED Driver Voltage Splitter For Use With Low Voltage Lighting Transformers

RS Stock 714-1397



## Specifications

- With 6 sockets (female contacts) for connectors type MINI MATE-AND-LOK.
- Ultra compact size.
- Maximum load per socket: 35 W - 3 A.
- Maximum total load: 120 W - 10 A.
- Supplied complete with 25 cm ribbon cable (type H03VVH2-F/2x0,75 mm<sup>2</sup>)
- Available with securing slots.
- Upon request, grommets can be supplied to plug unused sockets.
- With 6 threaded terminal blocks and anti-shearing reeds, for cables with area up to 2,5 mm<sup>2</sup>
- Ultra compact size.
- Maximum load per socket: 100 W - 8 A.
- Maximum total load: 250 W - 20 A.
- Supplied complete with 25 cm single-pole cable (2,5 mm<sup>2</sup>) for connection to the transformer.
- With securing slots.