

406088

# Hand Scraper, 75 mm, Grey



Designed for cleaning small spaces and rounded equipment such as large bowls, this narrow hand scraper is ideal for loosening stubborn dirt, including pastry, chocolate and burnt food. The polypropylene material reduces the risk of scratching sensitive surfaces.

# Technical Data

Item Number	406088
Blade Thickness	3,3 mm
Material	Polypropylene
Complies with (EC) 1935/2004 on food contact materials <sup>1</sup>	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	25 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	4000 Pcs.
Quantity Per Layer (Pallet)	400 Pcs.
Box Length	290 mm
Box Width	195 mm
Box Height	175 mm
Length/Depth	75 mm
Width	18 mm
Height	210 mm
Gross Weight	0,06 kg
Net Weight	0,05 kg
Cubik metre	0,0003 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature <sup>3</sup>	-20 °C
Max. drying temperature	120 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
Recycling Symbol "5", Polypropylene (PP)	Yes
GTIN-13 Number	5705022013957
GTIN-14 Number (Box quantity)	15705028013989
Commodity Code	39241000
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.