





AP6038A

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Colour	Black
Product or component type	PDU
PDU type	Basic
Cord length	3.7 m
Provided equipment	Installation guide Safety guide

Complementary

Input Voltage	230 V 240 V	
Height	4.4 cm	
Width	38.8 cm	
Depth	12.6 cm	
Net weight	5.4 kg	
Mounting location	Front	
Mounting preference	No preference	
Input Plug Type	IEC 60309 63 A 2P + PE	
Mounting mode	Not rack-mountable	
Rack units	1U	
Mounting position	Horizontal	
Permissible voltage	200240 V	
Max line current	48 A	
Input current limits	48 A	
Load capacity	14500 VA	
Network frequency	50/60 Hz	
Outlet type and quantity	3 IEC 60320 C19	

Environment

Product certifications	CE		
	EAC		
	IRAM		
	VDE		

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	39.5 cm
Package 1 Width	19.5 cm
Package 1 Length	50 cm
Package 1 Weight	8.3 kg

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACh Regulation	REACh Declaration
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes