



Metal Cable Reel PROFESSIONAL 3xT13 PUR 3x1.5mm² 30m IP55 silver/black



Item No.: 50 00074
EAN Code: 7611007168544

Description

Metal Cable Reel PROFESSIONAL 3xT13 with hinged cover, PUR cable H07BQ-F 3G1.5mm² orange, cable length 30m, T13 plug, thermal circuit breaker, robust and suitable for construction sites (K2), IP55, silver/black

Specifications

Type	Cable Reel
Brand	STEFFEN
Model	Professional
Reel	Galvanised Metal
Reel Colour	Silver
Number of Sockets	3
Socket Type	Type 13 IP55
Socket Colour	Anthracite, Blue
Cable Type	H07BQ-F (PUR)
Number of Conductors	3
Conductor Cross-Section	1.5 mm ²
Cable Length	30 m
Cable Colour	Orange

Rated Current	10 A
Rated Voltage	250 V
Rated Frequency	50 - 60 Hz
Rated Power Uncoiled	2500 W
Rated Power Coiled	1000 W
Plug Type	Type 13 IP55
Stand	Metal
Stand Colour	Silver
Halogen-Free	No
UV Resistance	High
Application	Indoor, Outdoor
IP Rating	IP55
K2 Suitable for Construction Sites	Yes
Operating Temperature Range	-25...+55 °C
Safety Features	Thermal Circuit Breaker
Product Height	370 mm
Product Width	280 mm
Product Depth	180 mm
Net Weight	5.130 Kg
Packaging	Cardboard Box
Electrified	Yes