SIEMENS

Data sheet 8PQ2015-6BA27

Masking frame 3VA11 (160 A), 3 or 4-pole, fixed-mounted, drive: direct, front-mounted rotary operator, motorized operating mechanism, RCD: with, H: 150 mm W: 600 mm



Model	
product brand name	SIVACON S4
design of the surface	powder-coated
net weight	0.74 kg
height	150 mm
width	600 mm
depth	10 mm
installation width for cabinet installation	600 mm
mounting height for device equipment can be used	150 mm
material	sheet-steel
reference code according to IEC 81346-2	UC

Approvals Certificates

General Product Approval	other
Miscellaneous	Confirmation

Environment

Environmental Con-firmations	Environmental Con-firmations

Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information- and Downloadcenter (Catalogs, Brochures,…)
http://www.siemens.com/lowvoltage/catalogs
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2015-6BA27
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/8PQ2015-6BA27
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2015-6BA27
CAx-Online-Generator
http://www.siemens.com/cax
Tender specifications
http://www.siemens.com/specifications

Subject to change without notice
© Copyright Siemens

last modified:	5/26/2025

Subject to change without notice
© Copyright Siemens

Subject to change without notice
© Copyright Siemens