

BALL VALVES

RSI - Parallel brass lever ball female-female valves



Part number	Material	Female thread	Temperature min/ max (°C)	Max. operating pressure	Net weight (Kg)	Dim. A (mm)	Dim. B (mm)
RSI 21	Brass	G1/2	-10.00 / 80.00	40.00	0,251	50.00	25.00
RSI 27	Brass	G3/4	-10.00 / 80.00	40.00	0,335	54.00	31.00

