




LOC		DIST		REVISIONS			
GP		00		P	LTR	DESCRIPTION	DATE
				Z2		REVISED PER ECO-11-005033	23MAR11

2.494	2.400	24	25	2-487526-4
2.394	2.300	23	24	2-487526-3
2.294	2.200	22	23	2-487526-2
2.194	2.100	21	22	2-487526-1
2.094	2.000	20	21	2-487526-0
1.994	1.900	19	20	1-487526-9
1.894	1.800	18	19	1-487526-8
1.794	1.700	17	18	1-487526-7
1.694	1.600	16	17	1-487526-6
1.594	1.500	15	16	1-487526-5
1.494	1.400	14	15	1-487526-4
1.394	1.300	13	14	1-487526-3
1.294	1.200	12	13	1-487526-2
1.194	1.100	11	12	1-487526-1
1.094	1.000	10	11	1-487526-0
.994	.900	9	10	487526-9
.894	.800	8	9	487526-8
.794	.700	7	8	487526-7
.694	.600	6	7	487526-6
.594	.500	5	6	487526-5
.494	.400	4	5	487526-4
.394	.300	3	4	487526-3
.294	.200	2	3	487526-2
.194	.100	1	2	487526-1
C REF	B	A	NO OF POSNS	PRODUCT PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. BERRY CHK D. DOLLYHIGH APVD —	12-11-85 12-13-85 —	TE Connectivity	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-9024 APPLICATION SPEC 114-16015	NAME	HOUSING, RECEPTACLE, LATCH, POLARIZED, FFC	
MATERIAL THERMOPLASTIC,	FINISH —	WEIGHT —	SIZE A2	CAGE CODE 00779	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV Z2