



### Main

Enclosure type	Weatherproof enclosure
Range of product	Kaedra
Device short name	Kaedra for modular devices with interface
Accessories included with enclosure	1 marking kit 1 plate for pushbutton controls 1 terminal block 16 holes 1 terminal block support 1 wiring strap

### Complementary

Enclosure mounting	Surface
Type of front cover	Reversible Transparent
Number of horizontal rows	1
Number of 18 mm modules per row	18
Total number of 18 mm modules	12
Type of rail	DIN
Number of openings of interface	1
Base dimension	90 x 100 mm
Number of plates	1 for pushbutton controls
Number of pre-cutouts PG ISO	17
Number of terminal blocks	1 with 16 outgoers
Locking options description	Optional keylock
Enclosure material	Plastic
Width	448 mm
Height	280 mm
Depth	160 mm
Colour	Door : transparent green Enclosure : light grey ( RAL 7035 )

### Environment

Standards	EN 50102 EN 50262 IEC 60439-3 IEC 60529 IEC 670
Fire resistance	750 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Electrical shock protection class	Class II
Ambient air temperature for operation	-25...60 °C
RoHS EUR conformity date	0648
RoHS EUR status	Compliant