

## **FEATURES**

- Available in 2, 3 and 4 tread steps
- Non-slip tread
- Working load of up to 150kg
- Steel Construction
- Rubber handle
- Non-slip ribbed rubber treads to help you climb more safely
- Foldable design

# RS PRO 2 Tread Steel Steps 0.49m Platform Height, Silver Grey

RS Stock No.: 877-6815



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

Introducing folding step ladders from RS PRO, a range of high quality and convenient step ladders ideal for use in a wide range of environments. This range of step ladders are the perfect solution for gaining extra height to access areas out of reach. The step ladders feature a steel framework construction complete with a soft and comfortable handle and plastic floor protectors. The treads (steps) feature non-slip ribbed rubber providing extra grip and stability for the user when in use. The steps can also be easily folded for convenience, allowing them to be stored in a cupboard to save space in areas with limited space. This range of folding step ladders from RS PRO are ideal use in a range of applications and are available in tread sizes 2, 3 and 4.

What sizes are available?

2 Tread: 877-6815
3 Tread: 877-6819
4 Tread: 877-6828

#### **General Specifications**

Number of Steps	2
Material	Steel
Colour	Silver Grey
Applications	Home, Office, Garage, Workshop, Store room

## **Mechanical Specifications**

Overall Dimensions	775mm x 485mm x 510mm		
Overall Height	0.775m		
Overall Width	485mm		
Overall Depth	510mm		
Folding Dimensions	890mm x 135mm x 485mm		
Working load	150kg		
Distance Between Treads	230mm		



Platform Dimensions	
Height	490mm
Top Tread Width	380mm
Top Tread Depth	260mm



Description	Open size H x W x D (mm)	Folding size H x W x D (mm)	Tread W x D (mm)	Platform Height (mm)	RS Stock No.
Step Ladders 2 Tread	775 x 485 x 510	890 x 135 x 485	380 x 260	490	877-6815
Step Ladders 3 Tread	1065 x 490 x 665	1220 x 140 x 490	380 x 260	710	877-6819
Step Ladders 4 Tread	1290 x 490 x 830	1475 x 145 x 490	380 x 260	930	877-6828

