

## Datasheet

# RS Pro Digital & Programmable HVAC Thermostat, 7 (Individual)/5 (Weekday)/1 days with LCD Display

RS Stock No: **823-4939**



## Product Details

RS Pro digital and programmable HVAC thermostat comes with LCD display for effective measurements. This wireless programmable thermostat kit can be used to control individual areas, designed to be used with portable heating appliances. This Thermostat features a large LCD display and optional programming period of either 7 individual day's or separate 5 days (weekdays) and 1 Day/1Day (Sat and Sun) programming with 4 or 6 separate time and temperature periods per day. It separates its functions into two units, the receiver plug socket and control centre, which serves as a user interface and temperature sensing/controller. You can put the control centre in your required room and it can read and control the temperature of the living area while the receiver is situated besides the heating appliance.

## Features and Benefits

- Can be placed anywhere in the home to control the temperature of an area of the user's choice
- Not limited by power control wiring locations
- Link with the receiver via 433MHz RF, control distance 100M open site
- Large LCD display
- The screen displays the set temperature and the room temperature and time simultaneously
- Permanent user setting and program setting retention during power loss
- Optional temperature display of Celsius or Fahrenheit scale
- Both vacation mode and hold duration mode available for comfort and energy saving
- Optional programming period
- Display temperature recalibrates

**Specifications:**

Additional Features	LCD Display
Contact Rating	10 A
Contact Voltage	230 V ac
Maximum Temperature	+35°C
Minimum Temperature	+5°C
Program Duration	7 Days (Individual), 5 Days (Weekday), 1 Day
Supply Voltage	230 V ac
Temperature Range	+5 to +35°C