

EB-S41

DATASHEET / BROCHURE



For business or pleasure, this high-quality and easy-to-use SVGA, 3,300-lumen projector works equally well at home or in the office.

Don't let your need for a business projector hold you back from enjoying blockbusters on the big screen at home. This versatile SVGA projector can do both. Even when there's ambient light, its 3,300 lumens and 3LCD technology are capable of delivering a bright and clear picture. And its incredibly long lamp life means it's great value for money.

Bigger is better

Whether you're watching blockbusters or delivering a presentation, this projector can achieve an impressive 350-inch display. It's great quality too with 3LCD technology that makes the display up to three times brighter than competitor products². In addition to its bright and vivid colours, the 15,000:1 contrast ratio produces defined shadows and deep blacks. From family and friends to business colleagues and clients, it's sure to get everyone's attention.

High-quality, bright images

Even in bright rooms, this powerful yet affordable SVGA projector delivers exceptionally bright yet colourful images with clear details. It's all thanks to 3LCD technology, which produces an equally high White and Colour Light Output of 3,300 lumens.

Long-lasting solution

Looking for a long-term, hassle-free and affordable solution for your projection needs? With this model's long-lasting lamp light source, you could watch a film every day for 15 years¹.

Stress-free set up

Here's a projector that's designed with portability and quick set up in mind. The carry case makes it easy to move from room to room, and you can quickly position the image with keystone correction and access content simply with the HDMI inputs. Thanks to the optional ELPAP10 adapter, it offers Wi-Fi connectivity, allowing you to share content from a smart device using the iProjection app.

KEY FEATURES

- **Create the big screen experience**
From box sets to business presentations, capture everyone's attention
- **Bright even with ambient light**
Equally high White and Colour Light Output of 3,300 lumens
- **Affordable, high-tech equipment**
Enjoy this SVGA projector
- **Long-lasting solution**
Watch a film every day for 15 years¹
- **Portable and quick to set up**
Transport with a carry case and keystone slider for easy alignment



EPSON
EXCEED YOUR VISION

PRODUCT SPECIFICATIONS

TECHNOLOGY

Projection System	3LCD Technology, RGB liquid crystal shutter
LCD Panel	0.55 inch with D7

IMAGE

Colour Light Output	3,300 lumen - 2,050 lumen (economy) in accordance with IDMS15.4
White Light Output	3,300 lumen - 2,050 lumen (economy) in accordance with ISO 21118:2012
Resolution	SVGA, 800 x 600, 4:3
Contrast Ratio	15,000 : 1
Lamp	UHE, 210 W, 6,000 h durability, 10,000 h durability (economy mode)
Keystone Correction	Auto vertical: $\pm 30^\circ$, Manual horizontal $\pm 30^\circ$
Colour Reproduction	upto 1.07 billion colours

OPTICAL

Projection Ratio	1.45 - 1.96:1
Zoom	Digital, Factor: 1.35
Image Size	30 inches - 350 inches
Projection Distance Wide/Tele	1.77 m - 2.4 m (60 inch screen)
Projection Lens F Number	1.44
Focal Distance	16.7 mm
Focus	Manual
Offset	8 : 1

CONNECTIVITY

USB Display Function	2 in 1: Image / Mouse
Interfaces	USB 2.0 Type A, USB 2.0 Type B, VGA in, HDMI in, Composite in, Cinch audio in, Wireless LAN IEEE 802.11b/g/n (WiFi 4) (optional)
Epson iProjection App	Ad-Hoc / Infrastructure

ADVANCED FEATURES

Security	Kensington lock, Security cable hole, Wireless LAN unit lock, Password protection
3D	No
Features	AV mute slide, Automatic keystone correction, Built-in speaker, Horizontal and vertical keystone correction, Long lamp life, Quick Corner
Video Colour Modes	Blackboard, Cinema, Dynamic, Presentation, sRGB

GENERAL

Energy Use	282 W, 203 W (economy), 0.2 W (standby), On mode power consumption as defined in JBMS-84 257 W
Product dimensions	302 x 237 x 82 mm (Width x Depth x Height)
Product weight	2.5 kg
Noise Level	Normal: 37 dB (A) - Economy: 28 dB (A)
Loudspeaker	2 W
Room Type / Application	Home Office, Home Photo, Streaming, TV & Box sets
Positioning	Ceiling Mounted, Desktop

OTHER

Warranty	24 months Carry in, Lamp: 12 months or 1,000 h Optional warranty extension available
----------	---

EB-S41

WHAT'S IN THE BOX

- Main unit
- Power cable
- Quick Start Guide
- Remote control incl. batteries
- User manual (CD)
- Warranty card
- Carrying Case
- VGA cable

OPTIONAL ACCESSORIES

- Wireless LAN Adapter - ELPAP10
V12H731P01
- ELPLP96
V13H010L96
- Air Filter - ELPAF32
V13H134A32
- Soft Carry Case - ELPKS69 - EB-x05/x41/x42, EH-TW6 series
V12H001K69
- Ceiling Pipe (700mm) - ELPPFP14
V12H003P14
- Ceiling Pipe (450mm) - ELPPFP13
V12H003P13
- Ceiling Mount (White) - ELPMB23
V12H003B23

LOGISTICS INFORMATION

SKU	V11H842041
EAN code	8715946639543
Country of Origin	Philippines
Layer	6 Units
Layer Block	6 Units

EB-S41



3LCD



For more information please contact:

Home users: 0343 90 37766
Business users*: 0871 42 37766
Republic of Ireland: 01 436 7742
Or visit us at <https://www.epson.co.uk/contactus>
* 10p per minute plus network extras.

Web: www.epson.co.uk
www.epson.ie

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.
Last extracted: 2018-09-27

1. Based on watching an average 1hr 45mins film every day and the lamp set in Eco mode.
2. Colour brightness (Colour Light Output) in brightest mode, measured by a third-party lab in accordance with IDMS 15.4. Colour brightness will vary depending on usage conditions. Top-selling Epson 3LCD projectors versus top selling 1-chip DLP projectors based on PMA research sales data for Dec 2015 through Nov 2016.

EPSON[®]