

Technical data sheet

Article number:
190-00336

SNP1.5



Product Group	Snapper hose clips for tubes and harnesses
Product Family	SNP-Series
Material	Polyamide 6.6, glass-fibre reinforced (PA66GF15)
Colour	Black (BK)
Application Tool	MSNP1-70
Bundle Ø max.	9.2 mm
Bundle Ø min.	7.8 mm
Fixation Method	Plug-in mounting
Flammability	UL 94 HB
Operating Temperature	-40 °C to +105 °C
Package Content packed in	bag
ROHS compliant	Yes
Variant	Closed

RoHS ✓