

FEATURES

- Discharge duration is 3hrs
- Operating temperature range is between -25°C and 50°C
- Luminosity 2000lm
- Fitting type is batten

LED Emergency Lighting Batten 20 W

RS Stock No.: 176-8558



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 2ft 20W LED Emergency NCF.240V grey light with a high lumen output. This light is ideal for industrial and commercial applications such as warehouses, car parks, Arena's. With an ultra-durable Polycarbonate body and diffuser and aluminium tray, they are extremely lightweight and provide an even light distribution. The light is supplied pre-fitted with stainless steel 304 clips making them an ideal fitting for food preparation areas.

General Specifications

Lamp Type	LED
Light Style	Downlight
Luminosity	2000lm
Lumen Efficiency	100lm/W
Maintained	Maintained
Colour Temperature	6300K, Daylight
Finish	Grey
Beam Angle	120°
Material	Aluminium + Polycarbonate
Duration	3h
Applications	Emergency exits, Switch rooms, Storage areas

Electrical Specifications

Wattage	20W
Voltage Rating	100V to 277V ac

Mechanical Specifications

Length	600mm
Width	94mm
Fitting Type	Batten

Operation Environment Specifications

Environment Temperature	-25°C to 50°C
-------------------------	---------------

Protection Category

IP Rating	IP65
-----------	------

Approvals

Compliance/Certifications	RoHS, IK08
---------------------------	------------



