



MATERIAL FACT SHEET

403616 R02CPU

General Data

Product Hierarchy	IAD51401
	Modular PLC
	IQ-R Standard
Ext. Material Group	10 STANDARD ITEM
ABC Indicator	B (Limited Availability from Stock)

e-shop: <https://emea.mitsubishielectric.com/fa/shop/material-page/000000000000717286>

FA-MOD PLC: CPU Module

Series	MELSEC IQ-R SERIES
Type	STANDARD CPU
Program Memory	20K
Program Memory Unit	STEPS
Local I/O Points	4096
Local + Remote I/O Points	8192
Cycle Time LD (ns)	3,92
Cycle Time MOV (ns)	7,84
USB	1
Ethernet Port	1
Buffer Battery	YES
Int. Current Consumption (A)	0,67

Product Dimensions & Weight

Width (mm)	27,8
Height (mm)	106
Depth (mm)	110
Weight (kg)	0,2

Logistic Dimensions & Gross Weight

Length (cm)	16,5
Width (cm)	15,0
Height (cm)	4,5
Gross Weight (kg)	0,223
Volume (cdm)	1,114

Stock Data

Planned Delivery Time (Days)	94
------------------------------	----

Life Cycle

Sales Start	27.07.2018
Predecessor	266161 / Q03UDVCP

Additional Product Information

Binding Tariff Information	DEBTI-52748/20-1
BTI validity date	27.06.2024
Battery included	NO

Export Data

Commodity Code	85371091
Legal Control (Dual Use List)	Not Listed
Country of Origin	Japan (JP)
Preference Status (Supplier Declaration)	Non EU

Environmental

REACH Limit Exceeded	YES
----------------------	-----

REACH Substance CAS Number	1303-86-2
REACH Substance CAS Number (2)	71868-10-5
REACH Substance CAS Number (3)	7439-92-1
REACH Substance CAS Number (4)	80-43-3
Dangerous Goods Class	NO
Dangerous Goods Identifier	NO
RoHS Compliance	COMPLIANT
WEEE	B2B

Conformity

CE	COMPLIANT
EAC	NON-COMPLIANT
UKCA	COMPLIANT

Documentation & Media Data

Manual URL Indicator	https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&doc-cats=bltdae25c2bd5f2ff94&q=R02CPU&doc-lang=en
Certificates URL Indicator	https://emea.mitsubishielectric.com/fa/advanced-search?ct=document&doc-cats=blt8050dd1408c11cc2&q=R02CPU&doc-lang=en

Product Packaging

Cardboard (g)	45
Other paper (g)	26
Aluminum (g)	0
Steel (g)	0
Styrofoam (g)	0
Other plastic (g)	3
Wood (g)	0
Glass (g)	0
Others (g)	0

Compatible products

Material	Description / Price List Text / Classification
165286	FX3U-32BL Battery Battery for PLC types FX3 / FX5 Class 100100112: FA-COM PLC: Spare Part
165286	FX3U-32BL Battery Battery for PLC types FX3 / FX5 Class 100101303: FA-OTHERS: Battery
221540	USB-CAB-5M USB 2.0 connection cabel, plug USB A to plug USB B (mini), 5m Class 100100303: FA-HMI: Cable
284378	GX Works3 2L-USB PLC Programming Software for MELSEC iQ-R/F, English, 2 Licences USB Class 100101201: FA-Software: Software PLC
284379	GX Works3 5L-USB PLC Programming Software for MELSEC iQ-R/F, English, 5 Licences USB Class 100101201: FA-Software: Software PLC
286227	iQ Works 2L-USB iQ Works V2.0,inc Navigator/GX/GT/MT Works/RT Toolbox3 inc SIM,Eng,2 Licence USB Class 100101201: FA-Software: Software PLC
286228	iQ Works 5L-USB iQ Works V2.0,inc Navigator/GX/GT/MT Works/RT Toolbox3 inc SIM,Eng,5 Licence USB Class 100101201: FA-Software: Software PLC
303426	iQ Works V02-15L0C-E iQ Works V2.0;incl Navigator,GX Works,GT Works,MT Works;engl;USB;15 PC's Class 100101201: FA-Software: Software PLC
304614	GX Works3 V01-2L0C-G PLC Programming SW; Melsec iQ-R/iQ- F only (no GXW2/GX Dev); USB; 2 PCs; German Class 100101201: FA-Software: Software PLC
304645	GX Works3 V01-5L0C-G PLC Programming SW; Melsec iQ-R/iQ- F only (no GXW2/GX Dev); USB; 5 PCs; German Class 100101201: FA-Software: Software PLC
308856	GX Works3 V01-2L0C-IT PLC Programming-S/W for Melsec iQ-R/iQ- F;engl;USB;2 PC's; Italian Class 100101201: FA-Software: Software PLC
338821	iQ Works V02-2L0C-G iQ Works V2.0;incl Navigator,GX Works,GT Works,MT Works;German;USB;2 PC's Class 100101201: FA-Software: Software PLC

Material	Description / Price List Text / Classification
339022	iQ Works V02-5L0C-G iQ Works V2.0;incl Navigator,GX Works,GT Works,MT Works;German;USB;5 PC's Class 100101201: FA-Software: Software PLC
401853	iQ Works V02-2L0C-IT iQ Works V2.0;incl Navigator,GX Works,GT Works,MT Works;Italian;USB;2 PCs Class 100101201: FA-Software: Software PLC
491761	Verbatim microSDHC Card 16GB Class 10 MicroSDHC memory card 16GB; Class 10; R/W: 10MB/s; adapter included Class 100100215: FA-MOD PLC: Other Option
612268	Transcend SDHC Card 8GB Class 4 SDHC memory card 8GB; Class 4; R: 18MB/s; W: 6MB/s Class 100100304: FA-HMI: Other Option
697551	IE-C6A-0.2m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 0.2m, for Cabinet Class 100100214: FA-MOD PLC: Cable
697582	IE-C6A-0.5m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 0.5m, for Cabinet Class 100100214: FA-MOD PLC: Cable
697583	IE-C6A-1.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 1.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
697584	IE-C6A-2.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 2.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
697585	IE-C6A-5.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 5.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
697586	IE-C6A-10.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 10.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
697587	IE-C6A-15.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 15.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
697588	IE-C6A-20.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 20.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
697589	IE-C6A-25.0m CC-Link IE Certified Patch Cable RJ45 Cat.6A, 25.0m, for Cabinet Class 100100214: FA-MOD PLC: Cable
697590	IE-CB-1piece CC-Link Bending tool for Patch Cable, RJ45, 1 piece, 90°Deg radius Class 100100215: FA-MOD PLC: Other Option
697591	IE-C6A-CON-1pc CC-Link IE Certified Patch Cable connector, easy clip, RJ45, Cat.6A, 1pc Class 100100215: FA-MOD PLC: Other Option
717285	EDS-G2008-EL 8Port Entry-level Unmanaged Switch,10/100/1000BaseT(X),CCLink IE Field/TSN Cl. A Class 100100211: FA-MOD PLC: Network Module
717286	EDS-G2005-EL 5Port Entry-level Unmanaged Switch,10/100/1000BaseT(X),CCLink IE Field/TSN Cl. A Class 100100211: FA-MOD PLC: Network Module