

Dust Extractor XGT®

VC006GM

Model VC006GM is a cordless M Class Dust Extractor powered by two 40Vmax XGT® Li-Ion batteries in series (80Vmax).

The main features and benefits are: High air flow similar to that of corded model. Automatic self-cleaning filter system (with twin filters). MAKPAC can be attached. Plastic tank with water drain for Wet/Dry use. Variable speed dial. Hose selection dial. Low air flow warning buzzer. AWS (Auto-start Wireless System)-compatibility. Equipped with water level sensor.



Technical specifications

Vacuum hose length	2,5 / 3,5 m
Vacuum hose diameter	28 / 38 mm
Voltage XGT	✓
Nominal Battery Voltage	2 x 40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	3,7 m³/min
Max. sealed suction	180 mbar
Suction power	350 W
Automatic Filter Cleaning System	✓
AWS ready	✓
Continuous Use XGT® 40V Max / 5.0 Ah X2	25 - 80 min
Tank Capacity for Dust	40 L
Tank Capacity for Liquids	30 L
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Product net weight	17,0 kg
Noise Uncertainty (K Factor)	2,5 dB(A)

User benefits

- Approved for Dust Class M in accordance with the EU standard
- GYUPPA automatic self-cleaning twin filter of our unique design removes dust from pre-filters during operation
- Variable speed
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Optional AC

1910N0-0

WATER FILTER SET FOR VC006G

1910Y4-9

Filter Bag 5 Piece Set

1911B5-2

PRE-FILTER SET

192563-1

Straight Pipe Ø 38 mm

198533-8

Flooring / carpet nozzle switch



1910R3-2

POLY BAG VINYL SET 10 PCS



1911B4-4

Damper Set for VC006G



192562-3

Curved hand tube 38 mm



195434-1

Hose Ø 38 mm x 2.5 m



199455-5

Floor Nozzle



Other

User manual

Parts drawing