



Part Number : [1300350068](#)
Product Description : DeviceNet Trunk Mini-Change Segmented Power Tee, 5 Pole, Male/Female with Female Drop
Series Number : 130035
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Number : DN3030-PT-1



Documents & Resources

Drawings
[1300350068_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c); 7(a) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130035
Description	DeviceNet Trunk Mini-Change Segmented Power Tee, 5 Pole, Male/Female with Female Drop
IP Rating	IP67
Product Name	DeviceNet Trunk
Type	Drop Tee
UPC	78678887060

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V

Physical

Color - Cable Jacket	Gray
Drop Connector	Mini-Change
Drop Gender	Female
Keyway	Single
LED Indicator	None
Left Trunk Connector	Mini-Change
Left Trunk Gender	Male
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Net Weight	93.439/g
Poles	5

Right Trunk Connector	Mini-Change
Right Trunk Gender	Female
Temperature Range - Operating	-20° to +105°C

This document was generated on Mar 27, 2025