

## 2-100

### Double ended ring spanner set

Code	ETIM
<b>6031120</b>	<b>EC011816</b>
EAN	UNSPSC
<b>4010886603116</b>	<b>27-11-17-05</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-01-06</b>
Customs tariff number	
<b>82041100</b>	



### Article description

- Most common sizes in a kit
- Acc. to DIN 838, ISO 3318, ISO 1085, ISO 10104
- Rings deep offset, strong but thin walls
- Vanadium steel 31CrV3, chrome-plated
- Satin non-glare finish
- Carefully forged and professionally machined:
- Ring: thin-walled, 5° deep offset from shaft, with UD profile for gentle transmission of force
- High bending strength - does not fracture or splinter when overloaded, thus minimising the risk of injury
- Overloading indicated by deformation
- For extremely deep or inset bolts
- Top-grade industrial quality for the hardest of continuous use

### Article parts list

6x7 8x9 10x11 12x13 14x15 16x17 18x19 20x22 24x27 30x32

### Article information

Contents (Qty of pieces)	<b>10</b>	Material	<b>31CrV3</b>
Version/Execution	<b>Rings deep offset, strong but thin walls</b>	Standard	<b>DIN 838</b> <b>ISO 3310</b> <b>ISO 1085</b> <b>ISO 10104</b>
Net weight [kg]	<b>2,555 kg</b>	Ring profile	<b>UNIT-DRIVE</b>
Surface	<b>chrome-plated</b>		