

Datasheet

ENGLISH

Brass Pneumatic Quick Connect Coupling, G 3/8 Female, Threaded

RS Stock number 667-1989

026 [Quick Release Pneumatic Couplings]

Order No



Interchangeability

TST 025,RECTUS 25, PARKER PE RECTUS 26, CEJN 320, JWL 520, JWL 530

Temperature Range

-20 C +100 C (-4 F +212 F)


Working Pressure

0 - 35 bar (0 - 500 PSI)

Flow Capacity

NW - 7,5

SUPER FLOW LINE



Standard version

Brass Nickel Plated Buna (M)

Options

F-Straight Flow

K - Chrome Plated

N - Nickel Plated

S - Stainless Steel

V - Viton Seal

Material

SW

Coupler Body: Laiton Brass Sleeve: Laiton Brass Valve: Laiton Brass Springs: Stainless Steel

Locking O-Ring: Stainless Steel

Lenght

Dia

Pims: Stainless Steel Seals: Buna (M)

Plug:Brass Nickel Plated

Couplers and Plugs	Connection	
Male Thread Coupler	G 1/8"	
	G 1/4"	
	G 3/8"	
	G 1/2"	
	M 14X1,5	
	M 16X1,5	
	M 18X1,5	
	G 1/4"	(
	G 3/8"	(
	G 1/2"	(
	M 14X1,5	(

	G 1/8"	026 EG 10	21	41	25
**************************************	G 1/4"	026 EG 13	21	41	25
	G 3/8"	026 EG 17	21	41	25
	G 1/2"	026 EG 21	21	44	25
Male Thread Coupler	M 14X1,5	026 EG 14	21	42	25
man conpres	M 16X1,5	026 EG 16	21	43	25
	M 18X1,5	026 EG 18	21	43	25
	G 1/4"	026 DG 13	21	41	25
0.082 880	G 3/8"	026 DG 17	21	41	25
	G 1/2"	026 DG 21	24	41	25
	M 14X1,5	026 DG 14	21	44	25
Female Thread Coupler	M 16X1,5	026 DG 16	21	41	25
	M18X1,5	026 DG 18	22	41	25



ENGLISH

	6 mm 1/4"	026 HU 06	21	55	25
	8 mm 5/16"	026 HU 08	21	55	25
	9 mm 5/14 "	026 HU 09	21	55	25
	10 mm 3/8"	026 HU 10	21	55	25
Standart Hose Barb Coupler	13 mm 1/2"	026 HU 13	21	55	25
	6 mm Parker 1/4"	026 HG 06 P	21	55	25
	10 mm Parker 3/8"	026 HG 10 P	21	58	25
	13 mm Parker 1/2"	026 HG 13	21	62	25
-87-28/-	6x8mm-m12x1	026 PG 06	21	60	25
	8x10mm- M16x1	026 PG 08	21	63	25
Plastic Hose Coupler	9x12mm- M16x1	026 PG 09	21	72	25
	6 mm-M12x1	026 MG 06	21	60	25
	8 mm-M12x1	026 MG 08	21	63	25
Panel Mound Standart Hose Coupler	10 mm-G1/4"	026 MG 10	21	72	25
Plastic Hose Coupler	6X8mm- M12X1	026 YG 06	21	133	25
	8x10mm- M16x1	026 YG 08	21	148	25
With Spring	9x12mm- M16x1	026 YG 09	21	148	25



ENGLISH

	6 mm1/4"	026 HU 06		46
	8 mm 5/16"	026 HU 08		46
	9 mm 5/14"	026 HU 09		46
	10 mm 3/8"	026 HU 10		46
	13 mm 1/2"	026 HU 13		46
Standart Hose Barb	6 mmParker 1/4"	026 HU 06 P		43
	10 mm Parker 3/8"	026 HU 10 P		46
	13 mmParker 1/2"	026 HU 13 P		50
	4X6-mm- M10X1	026 PU 04		34
	6X8mm- M112x1	026 PU 06		34
Plastic Hose Plug	8x10mm-12x1	026 PU 08		42
	3x12mm- M16x1	026 PU 09		42
	6 mm-M12x1	026 MU 06	14	56
Panel Mound Standard	8 mm-M12x1	026 MU 08	14	56
Hose Plug	10 mm-M14x1	026 PU10	17	56
	4X6mm- M10X1	026 YU 04		120
Plastic Hose Plug	6X8mm- M12x1	026 YU 06		120
With Spring	8x10mm- M16x1	026 YU 08		140
	9x12mm- M16x1	026 YU 09		140



ENGLISH

