

ALPHA WIRE
CUSTOMER PRODUCT SPECIFICATION

Part Number: 2920
Page 1 of 1 Pages

Issue: 2
Issue Date: 4/10/2017
Effective Date: 4/10/2017

- | A. Construction | Diameters (In) |
|--|---|
| 1) Component 1 | 1 X 1 HOOKUP |
| a) Conductor | 20 (19/32) AWG 10% Nickel Plated Copper |
| b) Insulation | 0.0055" Wall, Nom. ECA Fluoropolymer |
| (1) Tint Color | WHITE, BLACK, RED, GREEN, YELLOW, BLUE, BROWN
ORANGE, SLATE, VIOLET |
|
 | |
| B. Applicable Specifications | |
| 1) UL | AWM/STYLE 11540 300°C / 600 V _{RMS}
80C OIL
GAS RES
Horizontal Flame |
| 2) Other | Sunlight Resistant
Chemical Resistant
Water Resistant |
| 3) CE: | EU Low Voltage Directive 2014/35/EC |
| C. Environmental Compliance | |
| 1) RoHS Directive (2011/65/EU): | All materials used in the manufacture of this part meet the requirements of European Directive 2011/65/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. No Exemptions are required for RoHS Compliance on this item. Consult Alpha Wire's web site for RoHS C of C . |
| 2) REACH Regulation (EC 1907/2006): | This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration . |
| 3) California Proposition 65: | The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65. |
| D. Physical & Mechanical Properties | |
| 1) Temperature Range | -150 to 300°C |
| 2) Bend Radius | 10X Cable Diameter |
| 3) Pull Tension | 9.6 Lbs, Maximum |
| E. Electrical Properties | (For Engineering purposes only) |
| 1) Voltage Rating | 600 V _{RMS} |
| 2) Inductance | 0.03 µH/ft, Nominal |
| 3) Conductor DCR | 9.9 Ω/1000ft @20°C, Nominal |
| F. Other | |
| 1) Packaging | Flange x Traverse x Barrel (inches) |
| a) 1000 FT | 6.5 x 2 x 1.9 Continuous length |
| b) 100 FT | 2.75 x 1 x 1.125 Continuous length
<i>[Spool dimensions may vary slightly]</i> |
| 2) Notes: | |
| a) | Certain colors and put-up combinations may only be available by special order, minimums may apply. |

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability. Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.