



Infed terminal, 25 mm² IP20 Cable entry on the left with touch protection

Model	
product brand name	SENTRON
product designation	Busbar systems
design of the product	Accessories
Supply voltage	
operating voltage at AC rated value	690 V
Connections	
tightening torque	
• minimum	1 N·m
• maximum	2 N·m
type of connectable conductor cross-sections for copper conductor stranded	6 - 25 mm ²
Mechanical Design	
height	17.7 mm
width	17.5 mm
depth	14 mm
length	37 mm
net weight	10 g

Approvals Certificates		
General Product Approval	Declaration of Conformity	other

[Confirmation](#)

[Miscellaneous](#)



[Miscellaneous](#)

other	Environment
-------	-------------

[Confirmation](#)

[Environmental Conformations](#)

Further information

Siemens has decided to exit the Russian market (see here).
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.
 Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5ST3771-2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5ST3771-2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3771-2

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

8/15/2023 

