

## FEATURES

- **Flexible design:** Easily adapts to different shapes and surfaces for versatile installation
- **IP54 rating:** Protected against dust and splashes, suitable for indoor and certain outdoor applications
- **60 LEDs per metre:** Ensures consistent and bright illumination across the strip
- **16.6 mm LED pitch:** Provides uniform light distribution
- **85 lm/m luminous flux:** Delivers effective brightness for various lighting requirements
- **24 V DC voltage:** Compatible with standard power supplies for easy integration
- **5 m strip length:** Offers ample coverage for larger areas
- **8 mm strip width:** Slim profile for discreet installation

## RS PRO Flexible LED Strip Light, Yellow

RS Stock No: 558-403



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flexible LED strip light offers a versatile lighting solution for a variety of applications. With a bright yellow hue, it is ideal for both decorative and functional lighting needs. Its flexibility allows for easy installation in a range of settings, providing efficient illumination with a low power consumption of 4.8 W/m.

## General Specifications

|                              |                 |
|------------------------------|-----------------|
| Flexible/Rigid               | Flexible        |
| LED Colour                   | Yellow          |
| LED Pitch                    | 16.6 mm         |
| Number of LEDs Per Metre     | 60              |
| Product Type                 | LED Strip Light |
| Typical Luminous Flux (lm/m) | 85 lm/m         |

## Protection Category

|           |      |
|-----------|------|
| IP Rating | IP54 |
|-----------|------|

## Electrical Specifications

|                 |         |
|-----------------|---------|
| Power Per Metre | 4.8 W/m |
| Voltage         | 24 V dc |

## Approvals

|                     |          |
|---------------------|----------|
| Standards/Approvals | CE, RoHS |
|---------------------|----------|

## Mechanical Specifications

|              |      |
|--------------|------|
| Strip Length | 5 m  |
| Strip Width  | 8 mm |

